

Double nipple E-G1/2-1/2NPT

Part number: 9633

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal size	14.3 mm
Operating pressure complete temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque pneumatic connection 1	40 Nm
Max. tightening torque pneumatic connection 2	28 Nm
Nominal torque	47.9 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	47.68 g
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	1/2 NPT
Note on materials	RoHS-compliant