


# Short pulse valve VLK-3-PK-3

Part number: 9639

FESTO



 General operating condition

## Data sheet

Feature	Value
Nominal size	2.5 mm
Symbol	00992823
Operating pressure	2.5 bar ... 8 bar
Standard nominal flow rate (standardised to DIN 1343)	90 l/min
Explosion protection	The information in the certificate must be observed! Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	170 g
Type of mounting	On mounting frame
Material seals	TPE-U(PU)
Material housing	Die-cast zinc