

Plug socket MSSD-C-4P

Part number: 171157

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Type of mounting	On solenoid valve via M3 central screw
Mounting position	optional
Product weight	22 g
Electrical connection	3-pin Angled socket Type A To DIN EN 175301-803 Square design MSC Square design MSN1
Cable fitting	Pg 9
Cable diameter	6 mm ... 8 mm
Nominal cross section conductor	≤1.5 mm ²
Degree of protection	IP65
Ambient temperature	-25 °C ... 90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material housing	Polymer
Housing colour	Black