

# Vacuum filter VAF-PK-3

Part number: 535883

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal size	2 mm
Mounting position	optional
Grade of filtration	50 µm
Symbol	00991483
Operating pressure	-0.95 bar ... 0 bar
Note on operating pressure	Only for use in open vacuum systems
Flow rate with vacuum = -0.075 MPa (-0.75 bar, -10.875 psi)	50.8 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	0 °C ... 40 °C
Product weight	4 g
Type of mounting	In-line installation
Pneumatic connection	PK-3 with union nut
Material union nut	POM
Note on materials	RoHS-compliant
Material filter	Fabric PA
Material housing	PA
Suitable for ejector pulse	≤8 bar