


Intermediate pressure regulator plate LR-ZP-B-D-3

Part number: 35426

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Based on standard	ISO 5599-1
Design	Piston
Integrated function	Pressure regulator
Symbol	00991581
Pressure regulation range	0.05 MPa ... 1.2 MPa
Pressure regulation range	0.5 bar ... 12 bar
Pressure regulation range	7.25 psi ... 174 psi
Inlet pressure 1	≤14 bar
Inlet pressure 1	≤1.4 MPa
Inlet pressure 1	≤203 psi
Approval	UL – Recognized (OL)
LABS (PWIS) conformity	VDMA24364 zone III
Product weight	1220 g
Note on materials	RoHS compliant
Material seals	NBR
Material housing	Die-cast aluminium Steel