

Shock absorber DYSR-12-12-Y5-T

Part number: 1138643

FESTO



[General operating condition](#)

Data sheet

Feature	Value
Size	12
Stroke	12 mm
Cushioning	Adjustable
Mounting position	optional
Position detection	Without
Symbol	00995984
Max. impact speed	3 m/s
Reset time at room temperature	0.2 s
Reset time at min. ambient temperature	1 s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 80 °C
Cushioning length	12 mm
Max. stop force	900 N
Max. energy consumption per stroke	10.8 J
Max. energy consumption per hour	60000 J
Max. residual energy	0.05 J
Reset force	4.5 N
Min. insertion force	38 N
Product weight	120 g
Load range	90 kg
Type of mounting	Via lock nut
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	Galvanised steel
Material piston rod	High-alloy steel