




Safety Sub-functions
STO Category 1, up to PL c
PUS Category 1, up to PL c
SLT Category 1, up to PL c



Application Note
STO, PUS, SLT,
Category 1, up to PL
c

Title Application Note STO, PUS, SLT, Category 1, up to PL c
Version 1.0
Document number (TSHQ) 100223
Original German
Author Festo
Last date of saving 13.05.2019

Legal Notice

In the following, the “Festo AG & Co.KG” is designated as “Festo”.

This Example circuit is not binding. This example circuit outlines a possible solution for a sample application and makes no claim of completeness, especially with regard to configuration and equipment, as well as any eventualities for your actual application. The Example circuit is not a customised solution, it merely offers assistance with typical task assignments.

The values stated in the Example circuit are partly assumptions and assessments which do not replace a detailed examination based on EN ISO 13849 part 1 and 2.

The actual characteristic values that can be obtained (especially PL, PFH_D, category, DC, MTT_D, CCF) depend on the components used, as well as their conditions of use in the actual application.

The example circuit does not relieve you of the obligation to carry out a risk assessment and a validation of the specific application and to ensure the adherence to all specifications, especially the EC Machinery Directive 2006/42/EG. As the user, you are responsible for your specific application and for the correct operation of the described products.

Festo does not accept any liability for damages arising from the use of any incorrect or incomplete information contained in this documentation or any information missing therefrom. This equally applies to defects resulting from improper handling of devices and modules. In addition, all liability, with the exception of intent or gross negligence on the part of Festo, for damages arising due to non-adherence of the specifications of the EC Machinery Directive 2006/42/EG is also rejected.

The information in this document is in no way intended as a substitute for the operating instructions of the respective manufacturers or the design and testing of the application by the user. The operating instructions for products from Festo can be found at www.festo.com. Users of this document must themselves verify that all the functions described herein also work correctly in the application. Even after examining this document and using the specifications contained herein, users are nevertheless solely responsible for their own application.

Otherwise, all stipulations concerning liability included in the terms and conditions of delivery, payment and use of software from Festo, which can be found at www.festo.com and can be supplied on request, apply.

This document is only suitable for persons with sufficient expertise for machine safety based on EN ISO 12100 and EN ISO 13849. In addition, the following qualifications are required in the project team:

- Specialist in pneumatics
- Specialist in electrical engineering
- Specialist for the programming of control systems and safety switching devices

Copyright Notice

This documentation is the intellectual property of Festo, which also holds the exclusive copyright. Any modification of the content, duplication or reprinting of this documentation, as well as distribution to third parties, is only permissible with the express consent of Festo.

Festo reserves the right to make modifications to this document in whole or in part. All brand and product names are trademarks or registered trademarks of their respective owners.

© (Festo AG & Co.KG, D - 73734 Esslingen, 2019)

Internet: www.festo.com

E-Mail: service_international@festo.com

Table of Content

1	Example Circuits	4
1.1	SLT permanent, Category 1, up to PL c	5
1.1.1	Circuit Diagram	5
1.1.2	Components.....	5
1.1.3	Description.....	6
1.1.4	Safety Considerations	7
1.2	SLT switchable, Category 1, up to PL c	8
1.2.1	Circuit Diagram	8
1.2.2	Components.....	8
1.2.3	Description.....	9
1.2.4	Safety Considerations	10
2	Literature	10

1 Example Circuits

- The circuits specified in this document are principle circuits which cannot be complete due to their clarity and scope.
- The abbreviations used for the safety sub-functions refer to the definitions in VDMA 24584 [1] for pneumatics:
 - STO: Safe Torque Off
 - PUS: Prevention of unexpected start-up
 - SLT: Safely-limited torque
- Category and PL according EN ISO 13849-1 [2]
- The circuits and the procedure described are recommendations which do not exclude other possibilities.
- Due to the wide variety of possible valves, no valve type and part numbers can be given in this document. When selecting valves, make sure that the selected valves have the following characteristics:
 - Valve function: 5/3 exhausted (3/2 closed)
 - Type of actuation: electrical
 - Type of reset: mechanical spring
 - Sealing principle: soft
 - Type of piloting: piloted
 - Pilot air supply: internal or external
 - Duty cycle: 100%.
 - Well-tried components according to EN ISO 13849-1 and the relevant basic and well-tried safety principles have been observed.
 - B10 value required for the calculation of the $MTTF_D$ value must be available.


Important note

- In addition, further design features and requirements may exist, which must be determined depending on the application.

1.1 SLT permanent, Category 1, up to PL c

STO, PUS and SLT according VDMA 24584 [1] and category 1, up to PL c according EN ISO 13849-1 [2].




1.1.1 Circuit Diagram



1.1.2 Components

Component	Type	Description / Part Number / Remarks	Qty.	Mssr.
M20		Pneumatic drive	1	Festo
Q20		5/3 directional control valve, monostable	1	Festo
		Silencer, if necessary	2	Festo
R21	MS...-LR	Pressure regulator	1	Festo
S1		Acknowledge push button	1	
S2		Safety commanding device, e.g. emergency stop switch	1	
S20		Switch functional control	1	
T1		Safety switching device	1	

1.1.3 Description

Application	Double acting pneumatic drive, horizontal
Triggering event	Safety request, e.g. by emergency stop switch, safety gate
Reaction (Safety Sub-function)	<p>Safe torque off (STO), category 1, PL c</p>  <p>Prevention of unexpected start-up (PUS), category 1, PL c</p>  <p>Safely-limited torque (SLT), category 1, PL c</p> 
Safe state	<p>After a safety request (S2) the pneumatic drive is exhausted after an application-specific time and is energy-free. It is presumed that the exhausted state of the pneumatic drive is the safe state.</p> <p>The pneumatic drive cannot exceed a set force by limiting the pressure. It is presumed that this limitation is the safe state of the pneumatic drive.</p> <p>Notes:</p> <ul style="list-style-type: none"> • The precondition for the SLT safety sub-function is that no external forces are acting on the pneumatic drive (M20) that have not been taken into account. • The force of the drive can be changed with the pressure adjustment button of the pressure regulator. To prevent manipulation, sufficient measures must be taken to prevent manipulation, e.g. hidden installation.
Function	<p>By the safety request (S2):</p> <ol style="list-style-type: none"> 1. The input circuit of the safety switching device (T1) is interrupted. 2. The safe outputs of the safety switching device (T1) for the valve (Q20) are then switched off. 3. The solenoids of the valve (Q20) are no longer actuated. 4. The valve (Q20) switches to the normal position, separates the supply of the operating pressure and exhausts both chambers of the pneumatic drive (M20) via the valve (Q21). This exhausts the air from the pneumatic drive (M20). <p>Permanent force limitation</p> <ul style="list-style-type: none"> • The pressure is limited by the pressure regulator (R21) so that the pneumatic drive (M20) cannot generate a greater force.
Manual reset function	<ol style="list-style-type: none"> 1. After resetting the safety request (S2), e.g. by mechanically unlocking the emergency stop switch or closing the safety guard, the start or restart can be made possible by pressing the acknowledge push button (S1). 2. The safety switching device (T1) can then allow the solenoids of the valve (Q20) to be controlled so that normal operation is possible.


1.1.4 Safety Considerations

Input	Safety considerations must be carried out in accordance with the selected safety commanding device (S2).
Logic	Safety considerations must be carried out in accordance with the selected safety switching device (T1).
Output	The valve (Q20) and the pressure regulator (R21) are well-tried components according to EN ISO 13849-1 and the relevant basic and well-tried safety principles have been observed. B10 value required for the calculation of the $MTTF_D$ must be available.

1.2 SLT switchable, Category 1, up to PL c

STO, PUS and SLT according VDMA 24584 [1] and category 1, up to PL c according EN ISO 13849-1 [2].




1.2.1 Circuit Diagram



1.2.2 Components

Component	Type	Description / Part Number / Remarks	Qty.	Mssr.
M20		Pneumatic drive	1	Festo
Q20		5/3 directional control valve, monostable	1	Festo
Q21		3/2 directional control valve, monostable	1	Festo
		Silencer, if necessary	2	Festo
R20	OS-...-B; OS-PK-3	OR gate	1	Festo
R21	MS...-LR	Pressure regulator	1	Festo
S1		Acknowledge push button	1	
S2		Safety commanding device, e.g. emergency stop switch	1	
S20		Switch functional control	1	
S21		Operation mode switch	1	
T1		Safety switching device	1	

1.2.3 Description

Application	Double acting pneumatic drive, horizontal
Triggering event	Safety request, e.g. by emergency stop switch, safety gate
Reaction (Safety Sub-function)	<p>Safe torque off (STO), category 1, PL c</p>  <p>Prevention of unexpected start-up (PUS), category 1, PL c</p>  <p>Safely-limited torque (SLT), category 1, PL c</p> 
Safe state	<p>After a safety requirement (S2):</p> <ul style="list-style-type: none"> The pneumatic drive is exhausted after an application-specific time and is energy-free. It is presumed that the exhausted state of the pneumatic drive is the safe state. <p>In “manual” operating mode additionally:</p> <ul style="list-style-type: none"> The pneumatic drive cannot exceed a set force by limiting the pressure. It is presumed that this limitation is the safe state of the pneumatic drive. <p>Notes:</p> <ul style="list-style-type: none"> The precondition for the SLT safety sub-function is that no external forces are acting on the pneumatic drive (M20) that have not been taken into account. The force of the drive can be changed with the pressure adjustment button of the pressure regulator. To prevent manipulation, sufficient measures must be taken to prevent manipulation, e.g. hidden installation.
Function	<p>By the safety request (S2):</p> <ol style="list-style-type: none"> The input circuit of the safety switching device (T1) is interrupted. The safe outputs of the safety switching device (T1) for the valve (Q20) are then switched off. The solenoids of the valve (Q20) are no longer actuated. The valve (Q20) switches to the normal position, separates the supply of the operating pressure and exhausts both chambers of the pneumatic drive (M20) via the valve (Q21). This exhausts the air from the pneumatic drive (M20). <p>When switching from “automatic” mode to “manual” mode (S21)</p> <ol style="list-style-type: none"> The safety switching device (T1) detects the change from automatic mode to manual mode. The safe outputs of the safety switching device (T1) for the valves (Q20, Q21) are then switched off. The solenoids of the valves (Q20, Q21) are no longer actuated. The valve (Q21) switches to the normal position and thus the OR gate (R20) switches to the flow path with the pressure regulator (R21) to limit the pressure. The valve (Q20) switches to the normal position, separates the supply of the operating pressure and exhausts both chambers of the pneumatic drive (M20).
Manual reset function	For the safety request (S2):

	<ol style="list-style-type: none"> 1. After resetting the safety request (S2), e.g. by mechanically unlocking the emergency stop switch or closing the safety guard, the start or restart can be made possible by pressing the acknowledge push button (S1). 2. The safety switching device (T1) can then allow the solenoids of the valve (Q20) to be controlled so that normal operation is possible. <p>Additionally in “automatic” operating mode:</p> <ol style="list-style-type: none"> 1. The operating mode switch (S21) is in the switching position for the operating mode “automatic”. 2. The safe output of the safety switching device (T1) for the valve (Q21) is then switched on. 3. The solenoid of the valve (Q21) is actuated. 4. The valve (Q21) switches to the switching position and the OR element (R20) switches to the flow path with the operating pressure. This means that the pressure is not limited and higher forces are possible. <p>Additionally in the “manual” operating mode:</p> <ol style="list-style-type: none"> 1. The operating mode switch (S21) is in the switching position for the “manual” operating mode. 2. The safe output of the safety switching device (T1) for the valve (Q21) remains switched off. 3. The solenoid of the valve (Q21) is not actuated. 4. The valve (Q21) remains in the normal position and the OR gate (R20) switches to the flow path with the pressure regulator (R21) to limit the pressure.
--	---

1.2.4 Safety Considerations

Input	Safety considerations must be carried out in accordance with the selected safety commanding device (S2).
Logic	Safety considerations must be carried out in accordance with the selected safety switching device (T1).
Output	The valves (Q20, Q21), the pressure regulator (R21) and the OR gate (R20) are well-trying components according to EN ISO 13849-1 and the relevant basic and well-trying safety principles have been observed. B10 value required for the calculation of the MTTF _D must be available.

2 Literature

- [1] VDMA 24584:2016-08 - Safety functions of regulated and unregulated (fluid) mechanical systems (German edition)
- [2] DIN EN ISO 13849-1:2016-06 - Safety of machinery - Safety-related parts of control systems - Part 1: General principles for design (ISO 13849-1:2015); German version EN ISO 13849-1:2015