

Certificate of Compliance

Issued to:

FESTO SE & CO. KG
Ruiter Strasse 82
73734 Esslingen Germany

This certificate confirms that representative samples of:
CABLE ASSEMBLIES AND FITTINGS FOR INDUSTRIAL CONTROL AND SIGNAL DISTRIBUTION
See addendum page for models

Has been evaluated by UL LLC in accordance with Standard(s) for Safety:

UL 2238, Cable Assemblies and Fittings for Industrial Control and Signal Distribution
CSA C22.2 No. 182.3, Special use attachment plugs, receptacles and connectors

Additional Information:

See UL Product iQ® at <https://iq.ulprospector.com> for additional information.

This Certificate of Compliance indicates that representative samples of the product described in the certification report have met the requirements for UL certification. It does not provide authorization to apply the UL Mark. Only the Authorization Page that references the Follow-Up Services Procedure for ongoing surveillance provides authorization to apply the UL Mark.

Only those products bearing the UL Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Certification Mark on the product.



David Piecuch
UL Mark Certification Program Owner

Certificate Number:

E474609

Report Reference:

E474609-20181220

Issue Date:

2024-01-04



Certificate of Compliance

Certificate Number: E474609
Report Reference: E474609-20181220
Issue Date: 2024-01-04

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Cable assemblies, double ended:

NEBC-M12G8-E-2-N-B-LE8, NEBC-M12G8-E-5-N-B-LE8, NEBC-M12G8-E-10-N-B-LE8, NEBC-M12G8-E-15-N-B-LE8, NEBC-M12G8-E-2-N-M12G8, NEBC-M12G8-E-5-N-M12G8, NEBC-M12G8-E-10-N-M12G8, NEBC-M12G8-E-15-N-M12G8, NEBC-M12W8-E-2-N-B-LE8, NEBC-M12W8-E-5-N-B-LE8, NEBC-M12W8-E-10-N-B-LE8, NEBC-M12W8-E-15-N-B-LE8, NEBC-M12W8-E-2-N-M12G8, NEBC-M12W8-E-5-N-M12G8, NEBC-M12W8-E-10-N-M12G8, NEBC-M12W8-E-15-N-M12G8, NEFC-M12G8-0.3-M12G5-LK,

Cable assemblies, double ended:

NEBC-D8G4-ES-0.3-N-S-D8G4-ET-G2, NEBC-D8G4-ES-0.3-N-S-D8G4-ET, NEBC-D8G4-ES-0.5-N-S-D8G4-ET-G2, NEBC-D8G4-ES-0.5-N-S-D8G4-ET, NEBC-D8G4-ES-1-N-S-D8G4-ET-G2, NEBC-D8G4-ES-1-N-S-D8G4-ET, NEBC-D8G4-ES-2-N-S-D8G4-ET-G2, NEBC-D8G4-ES-2-N-S-D8G4-ET, NEBC-D8G4-ES-5-N-S-D8G4-ET-G2, NEBC-D8G4-ES-5-N-S-D8G4-ET, NEBC-D8G4-ES-7.5-N-S-D8G4-ET-G2, NEBC-D8G4-ES-7.5-N-S-D8G4-ET, NEBC-D8G4-ES-10-N-S-D8G4-ET-G2, NEBC-D8G4-ES-10-N-S-D8G4-ET, NEBC-D8G4-ES-15-N-S-D8G4-ET-G2, NEBC-D8G4-ES-15-N-S-D8G4-ET, NEBC-D8G4-ES-20-N-S-D8G4-ET-G2, NEBC-D8G4-ES-20-N-S-D8G4-ET, NEBC-D8G4-ES-25-N-S-D8G4-ET-G2, NEBC-D8G4-ES-25-N-S-D8G4-ET, NEBC-D8G4-ES-30-N-S-D8G4-ET-G2, NEBC-D8G4-ES-30-N-S-D8G4-ET, NEBC-D8G4-ES-40-N-S-D8G4-ET-G2, NEBC-D8G4-ES-40-N-S-D8G4-ET, NEBC-D8G4-ES-50-N-S-D8G4-ET-G2, NEBC-D8G4-ES-50-N-S-D8G4-ET, NEBC-D8W4-ES-0.5-N-S-D8W4-ET-G2, NEBC-D8W4-ES-0.5-N-S-D8W4-ET, NEBC-D8W4-ES-1-N-S-D8W4-ET-G2, NEBC-D8W4-ES-1-N-S-D8W4-ET, NEBC-D8W4-ES-2-N-S-D8W4-ET-G2, NEBC-D8W4-ES-2-N-S-D8W4-ET, NEBC-D8W4-ES-5-N-S-D8W4-ET-G2, NEBC-D8W4-ES-5-N-S-D8W4-ET, NEBC-D8W4-ES-7.5-N-S-D8W4-ET-G2, NEBC-D8W4-ES-7.5-N-S-D8W4-ET, NEBC-D8W4-ES-10-N-S-D8W4-ET-G2, NEBC-D8W4-ES-10-N-S-D8W4-ET, NEBC-D8W4-ES-15-N-S-D8W4-ET-G2, NEBC-D8W4-ES-15-N-S-D8W4-ET, NEBC-D8W4-ES-20-N-S-D8W4-ET-G2, NEBC-D8W4-ES-20-N-S-D8W4-ET, NEBC-D8W4-ES-25-N-S-D8W4-ET-G2, NEBC-D8W4-ES-25-N-S-D8W4-ET, NEBC-D8W4-ES-30-N-S-D8W4-ET-G2, NEBC-D8W4-ES-30-N-S-D8W4-ET, NEBC-D8W4-ES-40-N-S-D8W4-ET-G2, NEBC-D8W4-ES-40-N-S-D8W4-ET, NEBC-D8W4-ES-50-N-S-D8W4-ET-G2, NEBC-D8W4-ES-50-N-S-D8W4-ET

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact UL Solutions Customer Service at <https://www.ul.com/contact-us>.

