

Push-in Y-connector QSY-8-4

Part number: 130610

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal size | 1.7 mm |
| Tubing insertion depth | 18.1 mm |
| Note on the tubing insertion depth | Ø4 depth 14.9 mm Ø8 depth 18.1 mm |
| Mounting position | optional |
| Design | Y-shape |
| Size of pack | 10 |
| Design | Push-pull principle |
| Operating pressure complete temperature range | -0.095 MPa ... 0.6 MPa |
| Operating pressure complete temperature range | -0.95 bar ... 6 bar |
| Operating pressure complete temperature range | -13.775 psi ... 87 psi |
| Temperature-dependent operating pressure | -0.095 MPa ... 1.4 MPa |
| Temperature-dependent operating pressure | -0.95 bar ... 14 bar |
| Temperature-dependent operating pressure | -13.775 psi ... 203 psi |
| Note on operating pressure | Water: max. 0.6 MPa at max. 50°C |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 4 according to ISO 14644-1 |
| Ambient temperature | -10 °C ... 80 °C |
| Product weight | 13 g |
| Number of outputs | 2 |
| Number of supply lines | 1 |
| Pneumatic connection, port 1 | For tubing outer diameter of 8 mm |
| Pneumatic connection, port 2 | For tubing outside diameter of 4 mm |
| Colour of release ring | Blue |
| Note on materials | RoHS-compliant |
| Material housing | PBT |
| Material release ring | POM |
| Material tubing seal | NBR |
| Material tubing clamp component | High-alloy stainless steel |