

Lubricator MS6-LOE-1/4-R

Part number: 529779

FESTO



[PDF General operating condition](#)

Data sheet

Feature	Value
Size	6
Series	MS
Mounting position	Vertical +/-5°
Design	Proportional standard mist lubricator
Max. oil capacity	75 cm ³
Bowl guard	Plastic bowl guard
Symbol	00991532
Operating pressure	1 bar ... 16 bar
Min. flow rate for lubricator function	50 l/min
Standard nominal flow rate (standardised to DIN 1343)	2500 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
Suitable for use with food	See supplementary material information
Media temperature	-10 °C ... 60 °C
Oil viscosity	ISO VG 32
Ambient temperature	-10 °C ... 60 °C
Product weight	600 g
Type of mounting	With accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Note on materials	RoHS-compliant
Material housing	Die-cast aluminium
Material bowl	PC