

Extra-deep/Oval

Type			N	S	U	F	NA
			NBR	SI	PU	FPM	BR
Material			Perbunan	Silicone	Polyurethane	Fluoro rubber	Perbunan/ antistatic
		PWIS-free	X			X	X
	Size	Shore hardness	Hs50°	Hs50°	Hs60°	Hs60°	Hs60°
ESS-15-E...	10,3	Stroke	2,0	2,2	2,1	2,2	
ESS-20-E...	11,2	Stroke	2,7	2,7	2,9	2,8	
ESS-30-E...	14,4	Stroke	4,1	4,5	4,2	4,1	
ESS-40-E...	17,5	Stroke	2,9	3,4	3,2	3,2	
ESS-50-E...	19,5	Stroke	4,4	4,8	4,2	4,2	
ESS-60-E...	28,5	Stroke	5,2	5,1	5,5	5,3	
ESS-80-E...	25,9	Stroke	5,3	5,2	5,1	5,1	
ESS-100-E...	25,7	Stroke	6,2	6,0	6,3	6,0	
ESS-4x10-O...	6,9	Stroke	1,9				
ESS-4x20-O...	6,8	Stroke	0,6				
ESS-6x10-O...	6,7	Stroke	0,8				
ESS-6x20-O...	6,9	Stroke	0,9				
ESS-8x20-O...	6,9	Stroke	1,0				
ESS-8x30-O...	6,9	Stroke	1,0				
ESS-10x30-O...	7,0	Stroke	1,2				
ESS-15x45-O...	18,3	Stroke	2,1				
ESS-20x60-O...	19,3	Stroke	2,7				
ESS-25x75-O...	20,6	Stroke	3,5				
ESS-30x90-O...	21,5	Stroke	4,3				