


# Plastic tubing, standard O.D.

Product range overview



Version	Type	Outside Ø [mm]	Colour										Operating medium			
			Silver	Blue	Black	Yellow	Green	Red	Brown	White	Natural	Blue/black	Compressed air	Vacuum	Water (not drinking water)	Mineral oil
	<b>PAN</b> Polyamide	4, 6, 8, 10, 12, 16	■	■	■	■	■	■	-	-	■	-	■	■	-	-
	<b>PAN-R</b> Polyamide	4, 6, 8, 10, 12, 16	■	-	-	-	-	-	-	-	-	-	■	■	-	-
	<b>PAN-VO</b> Polyamide	6, 8, 10, 12	-	■	■	■	■	■	■	■	-	-	■	■	■	■
	<b>PEN</b> Polyethylene	4, 6, 8, 10, 12, 16	■	■	■	■	■	■	-	-	■	-	■	■	-	-
	<b>PFAN</b> Perfluor-alkoxyalkan	4, 6, 8, 10, 12	-	-	-	-	-	-	-	-	■	-	■	■	-	-
	<b>PLN</b> Polyethylene	4, 6, 8, 10, 12, 16	■	■	■	-	-	■	-	-	■	-	■	■	■	-
	<b>PUN</b> Polyurethane	3, 4, 6, 8, 10, 12, 16	■	■	■	■	■	■	-	-	-	-	■	■	-	-
	<b>PUN-DUO</b> Polyurethane	4, 6, 8, 10	■	-	-	-	-	-	-	-	-	■	■	■	-	-
	<b>PUN-E</b> Polyurethane	4, 6, 8, 10, 12	■	■	■	-	-	-	-	-	-	-	■	■	-	-
	<b>PUN-CM</b> Polyurethane	4, 6, 8, 10, 12	-	-	■	-	-	-	-	-	-	-	■	■	-	-
	<b>PUN-H</b> Polyurethane	3, 4, 6, 8, 10, 12, 16	■	■	■	■	■	■	-	-	■	-	■	■	■	-
	<b>PUN-H-DUO</b> Polyurethane	4, 6, 8, 10	-	-	-	-	-	-	-	-	-	■	■	■	■	-
	<b>PUN-VO/-C</b> Polyurethane	6, 8, 10, 12	-	■	■	■	■	■	■	■	■	-	-	■	■	-