

Precizni regulator pritiska MS6-LRP-3/8-D4-A8

Broj dela: 538014

FESTO



[PDF](#) Opšti uslovi poslovanja

List sa podacima o pouzdanosti proizvoda

Informacije u ovom "Tehničkom listu o pouzdanosti proizvoda" zasnivaju se na nameni proizvoda. To uključuje poštovanje svih specifikacija u tehničkim listovima, katalogima, korisničkoj dokumentaciji i opštim uslovima rada. Korisnik je isključivo odgovoran za utvrđivanje da li je proizvod pogodan za određenu primenu.

Karakteristika	Vrednost
Common Cause Failure (CCF) measures ¹⁾	Observe compressed air quality Comply with maximum vibration and shock loads Comply with ambient temperature and temperature of medium Safely keep operating pressure within the limits of the technical specifications
Service-life value B ₁₀ ²⁾	10 Mio cycles
Vibration resistance	Transport application test with severity level 2 in accordance with FN942017-4 and EN 60068-2-6

- 1) CCF measures have to be verified for the precise application. Therefore, the list with measures is not meant to be exhaustive.
- 2) The ascertainment of characteristic service life values is based on the ISO 19973 "Pneumatic fluid power - Assessment of component reliability by testing".