


# Parallel kit EAMM-U-50-D32-42A-78

Part number: 1201607

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	50
Mounting position	Any
Gear unit ratio	1:1
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	12.1 kgmm <sup>2</sup>
Frictional torque independent of load	0.01 Nm
Transmittable torque	1 Nm
Product weight	610 g
Interface code, actuator	D32B
Interface code, motor in	42A
Note on materials	RoHS compliant