

Silencer AMTE-M-LH-N14

Part number: 1206990

FESTO



[PDF](#) [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Size of pack	20
Symbol	00991473
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Flow rate to atmosphere	3080 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7::-:]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Sound pressure level	82 dB(A)
Ambient temperature	-40 °C ... 80 °C
Product weight	17 g
Pneumatic connection	1/4 NPT
Material shock absorber insert	Bronze
Material screwed plug	Brass
Note on materials	RoHS compliant