

Solenoid coil MSN1G-24DC-OD

Part number: 123060

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	optional
Min. pick-up time	10 ms
Duty cycle	100%
Characteristic coil data	24 V DC: 2.5 W
Permissible voltage fluctuations	-15%/+10%
Approval	c UL us - Recognized (OL)
LABS (PWIS) conformity	VDMA24364-C1-L
Media temperature	-10 °C ... 50 °C
Degree of protection	IP65
Ambient temperature	-10 °C ... 50 °C
Product weight	80 g
Electrical connection	3-pin Type A To DIN EN 175301-803
Type of mounting	Clamped Via retaining clamp With accessories
Material housing	PA
Material electrical contact	Steel
Material winding	Copper