

# Rod clevis CRSG-M8

Part number: 13568

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	M8
Mounting position	Any
Based on standard	ISO 8140
Threaded connection	Female thread M8
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Ambient temperature	-40 °C ... 150 °C
Product weight	52.2 g
Material rod clevis	High-alloy steel
Note on materials	RoHS compliant
Material bolt	High-alloy steel
Material nut	High-alloy steel
Material lock	High-alloy steel