

Illuminating seal MEB-LD-12-24DC

Part number: 151717

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Switching position indicator	LED
Type of mounting	On solenoid valve via M2.5 central screw
Product weight	0.6 g
Electrical connection	Type C To DIN EN 175301-803 Square design MSEB
Operational voltage range DC	12 V ... 24 V
Protective conductor connection	Available
Nominal power illuminating seal	0.05 W
Degree of protection	IP65
Ambient temperature	-25 °C ... 85 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	TPE-U(PU)
Colour	Transparent