

# Illuminating seal MEB-LD-230AC

Part number: 151718

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Switching position indicator	LED
Type of mounting	On solenoid valve via M2.5 central screw
Product weight	0.6 g
Electrical connection	Type C To DIN EN 175301-803 Square design MSEB
Nominal operating voltage AC	230 V
Immunity to surge	2.5 kV
Protective conductor connection	Available
Nominal power illuminating seal	0.33 W
Permissible voltage fluctuations	+/-10%
Degree of protection	IP65
Ambient temperature	-25 °C ... 85 °C
CE mark (see declaration of conformity)	To EU Low Voltage Directive
UKCA marking (see declaration of conformity)	To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Pollution degree	3
Material housing	TPE-U(PU)
Colour	Transparent