

# Switch lug DASI-Q11-35/40-A-SL

Part number: 1548155

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	35 40
Design	For T-slot
For piston diameter	Ø35 Diameter 40
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	8 g
Type of mounting	Clamped in T-slot Via threaded pin Via female thread
Note on materials	RoHS-compliant
Material screws	Steel Galvanised