


Swivel flange SNCB-80

Part number: 174394

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|---|
| Size | 80 |
| Based on standard | ISO 15552 |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 5% by mass of copper are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils. |
| Ambient temperature | -40 °C ... 90 °C |
| Max. load capacity | 6 kN |
| Product weight | 636 g |
| Note on materials | RoHS compliant |
| Material mounting | Die-cast aluminium |
| Material bolt | Galvanised steel |
| Material bearing | Polymer |
| Material disc | Galvanised steel |
| Material screws | Galvanised steel |
| Material lock | Spring steel, galvanised |