

Trunnion flange ZNCF-80

Part number: 174415

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	80
Based on standard	ISO 15552
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	6 kN
Product weight	1296 g
Note on materials	RoHS compliant
Material mounting	Cast stainless steel
Material screws	Steel Galvanised