

# Clevis foot LSNG-50

Part number: 31742

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	50
Based on standard	VDMA 24562
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	2.5 kN
Product weight	416 g
Note on materials	RoHS compliant
Material mounting	High-alloy steel
Material rod end bearing	Steel PTFE