

Clevis foot LSNSG-63

Part number: 31750

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	63
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	4 kN
Product weight	370 g
Note on materials	RoHS compliant
Material mounting	Steel Galvanised
Material rod end bearing	Steel PTFE