

Clevis foot LBG-63

Part number: 31764

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	63
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils.
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	4 kN
Product weight	580 g
Product weight	20.44 oz
Note on materials	RoHS compliant
Material mounting	Cast stainless steel
Material bolt	Case-hardened steel
Material lock	Spring steel