

# Right angle clevis foot LQG-80

Part number: 31772

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	80
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	6 kN
Product weight	1126 g
Note on materials	RoHS compliant
Material mounting	Spheroidal graphite cast iron
Material bolt	Case-hardened steel
Material lock	Spring steel