

# Foot mounting DAMH-Q12-32

Part number: 3371845

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	32
Mounting position	optional
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Max. tightening torque	8 Nm
Product weight	287 g
Type of mounting	With through-hole
Note on materials	RoHS-compliant
Material bracket	Galvanised steel