

# Solenoid coil MSFG-12

Part number: 4526

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	Any
Switching position indicator	No
Min. pick-up time	10 ms
Duty cycle	100%
Characteristic coil data	12 V DC: 4.1 W
Permissible voltage fluctuations	+/-10%
LABS (PWIS) conformity	VDMA24364-C1-L
Degree of protection	IP65
Ambient temperature	-5 °C ... 40 °C
Max. tightening torque for socket	0.4 Nm
Product weight	55 g
Electrical connection	3-pin Plug pins with connection pattern to Festo standard for MSSD-F
Type of mounting	Via knurled nut
Note on materials	RoHS compliant
Material solenoid coil	Duroplast Copper Steel
Material winding	Copper