

Drive shaft adapter DARF-Q11-35/40

Part number: 4835939

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	35 40
For piston diameter	Ø35 Ø40
Design	Drive shaft adapter
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	350 g
Type of mounting	Via through-hole and centring sleeve
Note on materials	RoHS compliant
Material screws	Nickel-plated steel