

# Drive shaft adapter DARF-Q11-12

Part number: 4835942

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	12
For piston diameter	Ø12
Design	Drive shaft adapter
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	38 g
Type of mounting	Via through-hole and centring sleeve
Note on materials	RoHS compliant
Material screws	Nickel-plated steel