


Shock absorber YSRW-DGC-25-GF

Part number: 540348

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Size	25
Cushioning	Self-adjusting Soft characteristic curve
Mounting position	optional
Position detection	Without
Symbol	00991497
Max. impact speed	3 m/s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 80 °C
Type of mounting	Via lock nut
Note on materials	RoHS-compliant
Material piston rod	High-alloy steel