


# On/off valve MS12-EM-G

Part number: 541495

FESTO



[General operating condition](#)

## Data sheet

Feature	Value
Design	Piston gate valve
Type of actuation	Manual
Exhaust-air function	Cannot be throttled
Type of piloting	Direct
Symbol	00991309
Valve function	3/2-way, double solenoid
Operating pressure	0 bar ... 20 bar
lap	Overlap
Standard nominal flow rate (standardised to DIN 1343)	25000 l/min ... 32000 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [-:::]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Type of mounting	Either: Inline installation With accessories
Mounting position	Any
Flow direction	Non-reversible
Product weight	3900 g
Pneumatic connection, port 1	Manifold module
Pneumatic connection, port 2	Manifold module
Pneumatic connection, port 3	G1
Pilot air supply	Internal
Material seals	NBR
Material housing	Die-cast aluminium