

Electrical module VMPA2-FB-EMG-D2-4

Part number: 543334

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|---|
| Diagnosis | Condition monitoring Wire break per solenoid coil Short circuit of valves Undervoltage of valves |
| Max. number of valve positions | 2 |
| Max. number of valve coils | 4 |
| Internal current consumption, load voltage | 23 mA |
| Internal current consumption, operating voltage | 8 mA |
| Nominal pick-up current per solenoid coil | 99 mA up to 24 ms |
| Nominal current with current reduction | 18 mA after 24 ms |
| Corrosion resistance class CRC | (when installed) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 20 g |
| Material housing | POM |
| Note on materials | RoHS-compliant |