


# Throttle plate VABF-S3-2-F1B1-C

Part number: 543603

FESTO



[PDF](#) [General operating condition](#)

## Data sheet

Feature	Value
Construction width	18 mm
Based on standard	ISO 15407-1
Mounting position	Any
Vertical pneumatic linkage	Throttle plate, exhaust air flow control
Symbol	00991467
Operating pressure	-0.9 bar ... 10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C ... 50 °C
Product weight	228 g
Mounting with vertical stacking	On manifold sub-base On individual sub-base
Note on materials	RoHS compliant
Material housing	Die-cast aluminium