

Plastic tubing PEN-12X1,75-RT

Part number: 551478

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Outside diameter | 12 mm |
| Flow-relevant bending radius | 58 mm |
| Inside diameter | 8.4 mm |
| Min. bending radius | 33 mm |
| Tubing characteristics | Suitable for energy chains |
| Temperature-dependent operating pressure | -0.095 MPa ... 1 MPa |
| Temperature-dependent operating pressure | -0.95 bar ... 10 bar |
| Temperature-dependent operating pressure | -13.775 psi ... 145 psi |
| Note on operating pressure | Water: max. 0.6 MPa at 0 - 50 °C |
| Approval | German Technical Control Board (TÜV) |
| Certificate issuing authority | B 013277 0527 00 |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Element installed statically, no meaningful evaluation possible according to ISO 14644-1 |
| Ambient temperature | -30 °C ... 60 °C |
| Product weight according to length | 0.05423 kg/m |
| Pneumatic connection | For push-in connector outside diameter of 12 mm |
| Colour | Red |
| Shore hardness | D 52 +/-3 |
| Note on materials | RoHS compliant |
| Material tubing | Packaging unit |