

# Clevis foot LSN-40

Part number: 5562

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	40
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 120 °C
Max. load capacity	1.5 kN
Product weight	219 g
Note on materials	RoHS compliant
Material mounting	High-alloy steel
Material bushing	Wrought aluminium alloy
Material rod end bearing	Steel PTFE