

# Clevis foot LSN-100

Part number: 5566

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	100
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 120 °C
Max. load capacity	9 kN
Product weight	1166 g
Note on materials	RoHS compliant
Material mounting	Spheroidal graphite cast iron
Material bushing	Wrought aluminium alloy
Material rod end bearing	Steel PTFE