

# Electrical sub-base VAVE-L1-1VL1-LP

Part number: 566722

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Reverse polarity protection	Bipolar
Additional functions	Spark arresting
Signal status display	LED
Nominal operating voltage DC	12 V
Immunity to surge	0.8 kV
Pollution degree	3
Extended ambient temperature	-5 ... 60° C
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP40
Ambient temperature	-5 °C ... 50 °C
Mounting position	optional
Product weight	4.6 g
Connection cross section	0.14 mm <sup>2</sup>
Electrical connection	Flying lead
Cable length	0.5 m
Wire ends	Wire ferrule
Protective conductor connection	Not available
Type of mounting	Clip
Housing colour	Black
Note on materials	RoHS-compliant
Material housing	PA