

Cover plate VABB-L1-14

Part number: 569989

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Grid dimension	16 mm
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Approval	RCM trademark c UL us - Recognized (OL)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	23.9 g
Note on materials	RoHS-compliant
Material cover plate	Wrought aluminium alloy