

# Fixed flow restrictor VMPA-FT-NW1.7-10

Part number: 572550

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Valve function	Flow control function
Pneumatic connection, port 1	Sub-base
Type of mounting	Screw-in
Standard nominal flow rate in flow control direction	105 l/min ... 115 l/min
Operating pressure	-0.9 bar ... 10 bar
Ambient temperature	-5 °C ... 60 °C
Nominal size	1.7 mm
Mounting position	optional
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C ... 40 °C
Media temperature	-5 °C ... 60 °C
Product weight	0.04 g
Note on materials	RoHS-compliant
Material hollow bolt	Wrought aluminium alloy