

Manifold block VABM-B10-20S-G14-7-P3

Part number: 576470

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|-------------------------------|
| Grid dimension | 22 mm |
| Mounting position | optional |
| Max. number of valve positions | 7 |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 681 g |
| Type of mounting | With through-hole |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 3 | G1/4 |
| Note on materials | RoHS-compliant |
| Material manifold rail | Wrought aluminium alloy |