

# Clevis foot LBN-8/10

Part number: 6057

FESTO



 [General operating condition](#)

## Data sheet

| Feature  | Value   |
|--|---|
| Size   | 8/10  |
| Mounting position                                  | Any   |
| Corrosion resistance class CRC                     | 1 - Low corrosion stress  |
| LABS (PWIS) conformity                             | VDMA24364-B1/B2-L   |
| Suitability for the production of Li-ion batteries | Metals with more than 1% by mass of copper are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils. |
| Ambient temperature                                | -40 °C ... 150 °C   |
| Product weight                                     | 20 g  |
| Note on materials                                  | RoHS compliant  |
| Material mounting                                  | Steel<br>Galvanised   |
| Material bolt                                      | Steel<br>Galvanised   |
| Material lock                                      | Spring steel, galvanised  |