

Rod clevis SGA-M16

Part number: 6524

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	M16
Radial deviation +/-	5 mm
Angle compensation +/-	120 deg
Mounting position	optional
Threaded connection	Male thread M16
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 150 °C
Product weight	512 g
Note on materials	RoHS-compliant
Material bolt	Galvanised steel
Material rod eye	Steel Galvanised
Material lock	Spring steel, galvanised