

# Manifold rail VABM-L1-18W-G38-16-G

Part number: 8004921

FESTO



 [General operating condition](#)

## Data sheet

| Feature                        | Value                         |
|--------------------------------|-------------------------------|
| Grid dimension                 | 19 mm                         |
| Mounting position              | optional                      |
| Max. number of valve positions | 16                            |
| Approval                       | c UL us - Recognized (OL)     |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L             |
| Storage temperature            | -20 °C ... 60 °C              |
| Product weight                 | 3493 g                        |
| Pilot air port 12/14           | G1/8                          |
| Pilot exhaust port 82/84       | G1/8                          |
| Pneumatic connection, port 1   | G3/8                          |
| Pneumatic connection, port 2   | G1/4                          |
| Pneumatic connection, port 3   | G3/8                          |
| Pneumatic connection, port 4   | G1/4                          |
| Pneumatic connection, port 5   | G3/8                          |
| Note on materials              | RoHS-compliant                |
| Material manifold rail         | Wrought aluminium alloy       |