

# Manifold block VABM-B10-25S-G38-7-P3

Part number: 8026302

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Grid dimension	27.5 mm
Mounting position	optional
Max. number of valve positions	7
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	964 g
Type of mounting	With through-hole
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 3	G3/8
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy