

Manifold block VABM-B10-30S-G12-6

Part number: 8026381

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|-------------------------------|
| Grid dimension | 32 mm |
| Mounting position | optional |
| Max. number of valve positions | 6 |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 1776 g |
| Type of mounting | With through-hole |
| Pneumatic connection, port 1 | G1/2 |
| Pneumatic connection, port 3 | G1/2 |
| Pneumatic connection, port 5 | G1/2 |
| Note on materials | RoHS-compliant |
| Material manifold rail | Wrought aluminium alloy |