

# Roller lever VAOM-R4-20-D1-32

Part number: 8049235

FESTO



 [General operating condition](#)

## Data sheet

| Feature                        | Value                    |
|--------------------------------|--------------------------|
| Width                          | 20 mm                    |
| Type of actuation              | Mechanical               |
| Mounting position              | Movement plane           |
| Design                         | Roller lever             |
| Type of piloting               | Direct                   |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L        |
| Ambient temperature            | -10 °C ... 60 °C         |
| Type of mounting               | Screw-clamped            |
| Note on materials              | RoHS-compliant           |
| Material mounting adaptor      | Galvanised steel         |