

Plastic tubing PTFEN-6X1-NT-500

Part number: 8061178

FESTO



 General operating condition

Data sheet

Feature	Value
Outside diameter	6 mm
Flow-relevant bending radius	40 mm
Inside diameter	4 mm
Min. bending radius	38 mm
Instructions on use	Tubing without printing
Operating pressure complete temperature range	-0.095 MPa ... 0.5 MPa
Operating pressure complete temperature range	-0.95 bar ... 5 bar
Operating pressure complete temperature range	-13.775 psi ... 72.5 psi
Temperature-dependent operating pressure	-0.095 MPa ... 1.5 MPa
Temperature-dependent operating pressure	-0.95 bar ... 15 bar
Temperature-dependent operating pressure	-13.775 psi ... 217.5 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
Fire test material	UL94 V-0
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom suitability, measured according to ISO 14644-14	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Suitable for use with food	See supplementary material information
Ambient temperature	-20 °C ... 150 °C
Product weight according to length	0.034 kg/m
Pneumatic connection	For push-in connector O.D. 6 mm For barbed fitting outside diameter of 6 mm with union nut For barbed fitting I.D. 4 mm with union nut For barbed fitting I.D. 4 mm
Colour	Natural
Shore hardness	D 55 +/-5
Note on materials	RoHS compliant
Material tubing	PTFE