

Power supply unit CACN-3A-1-10-G2

Part number: 8149581

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width	42 mm
Height	130 mm
Length	160 mm
Mounting position	Open convection
Primary supply	Single phase
Input current	1.3 - 3.1 A
Nominal output voltage DC	24 V
Nominal output current	10 A
Input voltage range AC	100 V ... 240 V
Power failure bridging	20 ms
Mains frequency	45 Hz ... 65 Hz
Approval	c UL us - Listed (Oil)
CE mark (see declaration of conformity)	To EU EMC Directive To EU Low Voltage Directive
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-40 °C ... 85 °C
Relative air humidity	95%
Degree of protection	IP20
Ambient temperature	-25 °C ... 70 °C
Product weight	1168 g
Type of mounting	via DIN rail
Note on materials	RoHS compliant