

Quick exhaust valve SE-1/2-B

Part number: 9688

FESTO



 General operating condition

Data sheet

Feature	Value
Valve function	Quick exhaust
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Type of mounting	Screw-in
Standard nominal flow rate, exhaust 0.6-0.5 MPa (6-5 bar, 87-72.5 psi)	6480 l/min
Standard nominal flow rate, air flow 0.6-0.5 MPa (6-5 bar, 87-72.5 psi)	4560 l/min
Operating pressure	0.3 bar ... 10 bar
Ambient temperature	-20 °C ... 75 °C
Material housing	Die-cast aluminium
Operating medium	Compressed air to ISO 8573-1:2010 [7:--]
Nominal size	15 mm
Mounting position	Any
Symbol	00991459
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-20 °C ... 75 °C
Product weight	200 g
Pneumatic connection, port 3	G1/2
Material seals	NBR